

DESICCANT INSERTERS



RNA Feed Systems



LOW SPEED (DF-LS)
MEDIUM SPEED (DF-MS)

Product Features

- > **NO BOTTLE CHANGE PARTS!!**
- > Quick & repeatable changeovers, without tools
- > Insertion count verification with reject verification
- > Machined desiccant change parts are consistent and easy to maintain & clean.
- > Suitable for containers up to 4-1/4" wide
- > Speeds to 280/min. single insertion
- > Speeds to 120/min. triple insertion
- > 12 gal. capacity hopper bin built into frame for compact design.
- > Bin & elevator guides remove for cleaning and inspection. (no tools)
- > Allen-bradley touch screen
- > Stainless steel frame & anodized aluminum components
- > Designed for easy installation over existing conveyor



Options

- > Additional desiccant change parts
- > Casters
- > Larger hopper bin


Hopper/Elevator has a stainless bin and chute. FDA approved belting is flexible so as to not damage desiccants. The bin, guides, & chute are removable for cleaning—no tools.

Pre-Sorter has stainless liner. A disc change part is used to accurately align desiccants. Dust & safety cover provided.

Transfer Track (chute) is two machined Delrin halves. It's easy to clean on the inside and very sturdy. No-tool change over

Escapement Assembly is machined Delrin for long life and accuracy. This change part has quick disconnects and is non adjustable.

- Contact us about our other types of desiccant inserters:
- + Loose Pouch & Canister inserting—same machine
 - + Higher Speed unit for up to 800 per minute.



For further information, please contact **Andy Perks** at:

RNA Automation Limited
 Hayward Industrial Park, Tameside Drive
 Castle Bromwich, Birmingham B35 7AG
 Tel: +44 (0)121 749 2566
 Fax: +44 (0)121 749 6217
 Mobile: +44(0)7967 753505

